

PLUGSTATION®

EARPLUG DISPENSER, UNCORDED



KEEP AN EARFUL WITHIN EASY REACH

With the PlugStation, you can afford to put ear plugs in all the places they're needed. Hang one near workstations, another outside the restrooms and another in the break room. Easy, convenient access to hearing protection will help ensure that the earplugs are being used and will save time. Plus, each PlugStation comes with a free bracket.

INCREASED COMPLIANCE AND COST SAVINGS

Convenient, quick access and ease of use lead to higher compliance. Plus, because workers take one pair at a time there is no wasteful grabbing of multiple pairs or pocket fillups that end up getting trashed without being used. Less waste means more cost savings.

UNCORDED PLUGSTATIONS COME IN TWO SIZES – 250 PAIR & 500 PAIR

Choose the size that best suits your needs.

HYGIENIC FROM DISPENSER TO YOUR HAND

Unlike competitive dispensers, PlugStations are sealed to ensure that the plugs stay clean and sanitary. With PlugStations, earplugs drop right into the palm of your hand and when the PlugStation is empty simply toss it and hang a new one - no fumbling with messy, hard to use refills.

FEATURES

- Gives workers easy access to hearing protection.
- High visibility to increase awareness for your hearing conservation program.
- Eliminates the mess of individually bagged packaging because earplugs drop right into the palm of your hand.
- Each dispenser is sealed and disposable.
- All Moldex hearing protection is independently tested to AZ/NZS 1270.
- Look for the bright green colour as a symbol of Moldex quality.
- 100% PVC-Free for a greener alternative.

AVAILABLE EARPLUGS, 250 PR/500PR/PLUGSTATION



*PuraFit®
PlugStation, Uncorded
6844 – 250 Pairs
SLC 27dB*



*SparkPlugs®
PlugStation, Uncorded
6644 – 250 Pairs
6645 – 500 Pairs
6605 – 250 Pairs, Packaged
SLC 29dB*



*Gain' Green®
PlugStation, Uncorded
6647 – 500 Pairs
SLC 29dB*



*Mellows®
PlugStation, Uncorded
6846 – 250 Pairs
6847 – 500 Pairs
SLC 22dB*

PLUGSTATION®

EARPLUG DISPENSER, UNCORDED

PART # / DESCRIPTION	DISPLAY	CASE
6644 SparkPlugs PlugStation	250 Pairs	6 Dispensers
6645 SparkPlugs PlugStation	500 Pairs	4 Dispensers
6605 SparkPlugs PlugStation, Packaged	250 Pairs	4 Dispensers
6844 Pura-Fit PlugStation	250 Pairs	6 Dispensers
6845 Pura-Fit PlugStation	500 Pairs	4 Dispensers
6647 Goin' Green PlugStation	500 Pairs	4 Dispensers
6846 Mellows PlugStation	250 Pairs	6 Dispensers
6847 Mellows PlugStation	500 Pairs	4 Dispensers

WARNING TO USER

1. Use this laboratory-derived attenuation data for comparison purposes only. The amount of protection afforded in field use often is significantly lower depending on how the protectors are fitted and worn.
2. Failure to follow all instructions could result in hearing loss or injury.
3. Failure to obtain a proper fit will reduce effectiveness of hearing protectors and could result in hearing loss or injury.
4. Over protection can be dangerous. The wearer must be able to hear warning signals.
5. Wearers with hearing loss should exercise extreme caution.
6. It is the employer's responsibility to ensure that the type of hearing protector and its rating is appropriate for the user in their particular workplace.
7. Failure to follow these warnings could result in serious injury or death.
8. Moldex earplugs must only be used as part of a hearing conservation program that complies with applicable local safety and health regulations.

MOLDEX TECHNICAL ASSISTANCE

Moldex provides all of the technical assistance required to set up a hearing protection program. For more information call +1 (800) 421-0668 or +1 (310) 837-6500 ext. 512/550 or E-mail: tech@moldex.com or visit www.moldex.com.

Keep earplugs away from infants and small children as they may get caught in the windpipe and create a choking hazard.



MOLDEX®
Ideas that wear well.™

MOLDEX-METRIC, INC.
10111 Jefferson Blvd.
Culver City, CA 90232
TEL: +1 (800) 421-0668 or
+1 (310) 837-6500
FAX: +1 (310) 837-9563
E-mail: sales@moldex.com
www.moldex.com

AUSTRALIA
P.O. Box 4086
Carlingford North, NSW 2118
TEL: +61 (02) 9838 7588
E-mail: moldexaustralia@moldex.com
www.moldex.com

NEW ZEALAND
3 Spence Road
Henderson, Auckland, NZ
TEL: +64 (9) 837 8247
FAX: +64 (9) 837 8248
E-mail: moldexnz@moldex.com
www.moldex.com

ATTENUATION DATA FOR AUSTRALIA / NEW ZEALAND

Tested According to AS/NZS 1270 by Challis & Associates.

Note: For full details of methods of selecting a hearing protector, see AS/NZS 1269.3

Hearing protector Class 5 tested to AS/NZS 1270. When selected, used and maintained as specified in AS/NZS 1269.3, this protector may be used in noise up to 110dB(A) assuming an 85 dB(A) criterion.

A lower criterion may require a higher protector class.

Attenuation data for Pura-Fit Uncorded

Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	25.8	25.1	26.2	27.4	35.3	44.6	43.9	SLC₉₀ 27dB, Class 5
Standard Deviation (dB)	5.7	5.4	6.0	4.3	3.4	5.4	9.1	
Mean Minus Standard Deviation (dB)	20.1	19.7	20.2	23.1	31.9	39.2	34.8	

Attenuation data for SparkPlugs

Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	30.4	32.5	33.1	33.6	36.8	44.9	48.0	SLC₉₀ 29dB, Class 5
Standard Deviation (dB)	8.7	8.2	9.2	7.8	5.5	7.0	4.9	
Mean Minus Standard Deviation (dB)	21.7	24.3	23.9	25.8	31.3	37.9	43.1	

Attenuation data for Glide Foam Twist in Earplugs

Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	23.3	22.6	26.7	28.1	34.0	37.6	41.5	SLC₉₀ 24dB, Class 4
Standard Deviation (dB)	8.6	8.5	8.4	7.2	7.4	7.9	6.4	
Mean Minus Standard Deviation (dB)	14.7	14.2	18.3	20.9	26.7	29.6	35.1	

Attenuation data for Mellows

Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	19.0	20.1	24.6	24.6	31.1	36.0	39.7	SLC₉₀ 22dB, Class 4
Standard Deviation (dB)	6.8	7.2	8.5	6.2	5.2	8.3	8.6	
Mean Minus Standard Deviation (dB)	12.1	12.9	16.2	18.4	26.0	27.8	31.1	

LIMITED WARRANTY: IMPORTANT NOTICE TO AUSTRALIAN PURCHASER

This warranty is provided in addition to other rights and remedies you have under Australian law. Our goods come with guarantees which cannot be excluded under the Australian Consumer Law. You are entitled to replacement or refund for a major failure and to compensation for other reasonably foreseeable loss or damage. You are also entitled to have the goods repaired or replaced if the goods fail to be of acceptable quality and the failure does not amount to a major failure. This limited warranty is made in lieu of all other warranties, express or implied. There are no other warranties which extend beyond this limited warranty or those in the Australian Consumer Law in Schedule 2 to the Competition and Consumer Act 2010 as amended from time to time, or other similar legislation of a state or territory of Australia (Australian Consumer Law). The products sold will meet Moldex's physical standards and specifications. Subject to the Australian Consumer Law, remedies for breach of this limited warranty are limited to replacement of the number of Moldex products proved to have been defectively manufactured. Under this limited warranty, Moldex shall not be liable or responsible for any loss, damage or liability, direct, indirect, special, or consequential, arising out of sale, use, or misuse, or the inability to use products by the user, although you may have other rights and remedies under the Australian Consumer Law. Any claim under the warranty must be made within 1 year of the date of purchase of the product. To make a claim under the warranty, take the product (with proof of purchase) to the store where you purchased the product to contact Moldex. Moldex will pay your reasonable direct expenses of making a claim under this limited warranty which is upheld. You may submit details and proof of your expense claim to Moldex for consideration. This warranty is given by:

Moldex-Metric International LLC • ABN 64 964 843 487
10111 W Jefferson Blvd., Culver City, CA 90232, USA
+1 (310) 837-6500 • sales@moldex.com

